



## Shop Order

HME, Inc.  
 1950 Byron Center Ave.  
 Wyoming, MI 49519  
 616-534-1463  
 sales@hmetruck.com

HME, Inc.  
 1950 Byron Center Ave.  
 Wyoming, MI 49519  
 616-534-1463  
 sales@hmetruck.com

**Exp. Date:** 04/04/2018  
**Quote No:** 23186-0001  
**Job/Order No:** 23186  
**CHASSIS:** COMMERCIAL Commercial Chassis for HME Ahrens-Fox  
**PUMP:** TOP MNTV Pump Module, 47" Top Mnt, Volute Pump, Gen IV  
**BODY:** PUMPER Pumper Components & Equipment  
**WARRANTY:** WARRANTY Limited Warranty - Use For Contracts

03/25/2020

PART NO	S	DESCRIPTION	QTY	ID
		<b>== Commercial Chassis for HME Ahrens-Fox - 4.001 ==</b>	<b>1</b>	<b>HMC</b>
00-00-0014		NFPA-1901, 2016 Edition - Complete Apparatus - Comm Chassis	1	HMC
00-00-90SF	<b>S</b>	> Vocation and Basic Attributes - Apparatus	1	HMC
00-00-92SF	<b>S</b>	> Paint Codes and Basic Attributes - Apparatus	1	HMC
00-00-940C		Details of Construction - Order Confirmation	1	HMC
00-10-0112		HME Supplied Commercial Chassis	1	HMC
00-10-0230	<b>S</b>	> Commercial Chassis, Freightliner, M2-112	1	HMC
00-12-0010		No Front Bumper Extension Required	1	HMC
00-14-0010		Mud Flaps, Frt Axle, Black Rubber	1	HMC
00-14-0110	<b>S</b>	Fuel Tank Cover, ADP, L/S Frt Dr Step w/NFPA Stpng Srfc	1	HMC
00-14-0220	<b>S</b>	< Enclosure, ADP, R/S door steps, DPF box, with /NFPA Stpng Srfc	1	HMC
		Note: Reference #23102 R/S enclosure		
00-14-0250		No Add'l Ext Cab Compts Required At This Time	1	HMC
00-14-0310		No ADP Rear Cab Wall Protection Required	1	HMC
00-14-0780		Wheel Trim - Commercial Chassis	1	HMC
00-14-0800		-- No Wheel Paint Required	1	HMC
00-14-0900		-- No Wheel Pinstripe Required At This Time	1	HMC
10-X0-0100		-- Stainless 'Baby Moon' Caps & Nutcovers	1	HMC
10-X0-0300		-- Stainless "Lincoln Hat" Hub & Nut Covers	1	HMC
00-14-2060		No Cab Repaint Required	1	HMC
00-14-2210		Ember Separator, Air Intake	1	HMC
00-16-0102		LED Ground Lights, (2) Cab Mtd, Below Each Door, Two-Door	1	HMC
00-16-0200		Wiring Interface, Multiplex, Class 1 ES-Key Mgmt System	1	HMC
00-16-0410		Battery Disconnect Switch	1	HMC
00-16-0820		Auxiliary Engine Cooler	1	HMC
00-16-1410		Door Relective Material, NFPA Req'd, Comm Chassis, 2 Door	1	HMC
00-16-1515		No Map Box Required	1	HMC
00-20-SD00	<b>S</b>	Cab Console, Freightliner	1	HMC
00-20-SD02		-- No Console Options Required	1	HMC
40-X0-1401	<b>S</b>	-- Dual Port USB Charging Port in Center Console	1	HMC
09-F0-0100		No Air Inlet/Outlet Required	1	HMC
09-F0-0200		No Air Auto-Eject Required	1	HMC
09-X0-0100		No Onboard Air System Compressor Required	1	HMC
10-GW-0122		Tire Pressure Monitoring Device - 2 Axles - LED Alert	1	HMC
14-W0-1820		Modify Commercial Drivelines for Pump Installation	1	HMC
40-H0-1112		Dual Stutter Tone Air Horns - Commercial Chassis	1	HMC
40-H0-1124		-- Air Horn Mounting - Hood Sides	1	HMC

PART NO	S	DESCRIPTION	QTY	ID
40-H0-1201		-- Air Horn Circuit Powered - Battery and Ignition	1	HMC
40-H0-1210		-- Air Horn Control - Lanyard	1	HMC
40-H0-1302		-- Air/Elec Horn-Strg Wheel Cntrl - {Siren Switch Upgrade Here}	1	HMC
40-H0-2131		Electronic Siren - Whelen - Model 295SLSA1 - Comm	1	HMC
40-H0-5310		-- No Siren Switch Required	1	HMC
40-HA-2189		-- No Electronic Siren Rumbler Add-On Required	1	HMC
40-H0-3002		No Q2B/Super Chief Siren Required	1	HMC
40-H0-4002		No EQ2B Siren Required	1	HMC
40-HA-2010		Siren Speakers - Two - Cast Products - Recess Mtd	1	HMC
40-LC-0114		Open Compartment Light - Red Flashing - Whelen OS LED	1	HMC
40-LE-1001		Engine Maintenance Lights LED - Commercial	1	HMC
40-LM-1000		No Officer Maplight Required	1	HMC
40-LS-1000		No Cab Spotlights Required	1	HMC
40-LS-2000		No Handheld Spotlights Required	1	HMC
40-Y0-0010		No Intercom System Required	1	HMC
40-YC-3801		No Back-Up Camera Required	1	HMC
40-YS-0105		Handheld Light Options - Commercial Chassis	1	HMC
40-YS-2110		-- No Fire Vulcan Lights Required	1	HMC
40-YS-2210		-- No Fire Box Lights Required	1	HMC
40-YS-3210		-- No Survivor Lights Required	1	HMC
40-Z0-0002		No 12 VDC Power Point Outlet Required	1	HMC
40-Z0-0212		12VDC Power Circuits - Radio and/or Accessories - Comm	1	HMC
40-Z0-0364		-- Location - Cab Center Console - When Equipped - Comm	1	HMC
40-Z0-0380		-- No Additional 12 VDC Power Circuit Required	1	HMC
40-Z0-0852		NMO Mount - Radio Antenna Wiring - Centered - Comm	1	HMC
40-Z0-0856	S	-- Location - Center Console	1	HMC
40-Z0-0860		-- No Additional NMO Antenna Mount and Coax Required	1	HMC
40-Z0-9910		Fire Extinguisher and Hazard Triangle Kit	1	HMC
45-T0-0102		40 Amp - Battery Charger - ProMariner - Commercial	1	HMC
45-Z0-1202		-- Kussmaul 20 AMP - 120v - Super Auto Eject - Commercial	1	HMC
45-Z0-1302		-- Yellow Auto-Eject Cover	1	HMC
45-Z0-1322		-- Cab Exterior Mounted - Below the Driver's Door	1	HMC
71-10-0002		Diagnostic Cables and Software	1	HMC
71-10-0030		-- No Cummins Diagnostic Software Required	1	HMC
71-10-0060		-- No ABS/ATC Diagnostic Software Required	1	HMC
71-10-0070		-- No Allison Diagnostic Software Required	1	HMC
71-10-0100		-- No EsKey Modem Required	1	HMC
		<b>v4.001 - RELEASE DATE - 02/08/2018</b>	<b>1</b>	<b>HMC</b>
		<b>== Pump Module, 47" Top Mnt, Volute Pump, Gen IV - 4.001 ==</b>	<b>1</b>	<b>HME</b>
18-02-0200		No Xverse Cmpt -or- XLay/SpdLay BOC, Fwd of P/Encl Required	1	HME
20-02-0100		> HydraTechnology, Pump House Design Requirement	1	HME
20-02-0252		> Pump Enclosure, Top Mount, 47" Wide, Volute Pump, Gen IV	1	HME
20-04-1200		-- Walkway, Top Mnt, 96" W x 21" Frt/Bck w/ADP Stp Srfc	1	HME
20-04-0215		-- Running Boards, L/S, R/S w/ATP Step Surface	1	HME
20-04-0331		-- No LEFT Running Board Hosewell Required	1	HME
20-04-0332		-- No RIGHT Running Board Hosewell Required	1	HME
20-04-0420		-- LED Strip, Armor Guard, Runningboard, Pumphouse	1	HME
20-04-1400		-- No Walkway Grabrails Mounted on Cab Required	1	HME
20-04-2300		-- No Add'l Walkway Lights Required	1	HME
20-04-2599		-- No Mansaver Bars Required	1	HME
20-06-0210		-- No Walkway Storage Compts Required	1	HME
20-04-2005		-- Lights, (2) LED Walkway, Mtd Front of Module/Spdlays, Clear Lens	1	HME
20-04-2300		-- No Add'l Walkway Lights Required	1	HME
20-06-0800		-- Dunnage Compt, w/Floor	1	HME
20-06-1000		-- No Dunnage Compt Cover Required	1	HME
20-06-1610		-- Grabrails, (2) Access Dunnage Compt, Mtd L/ R Side of Compt	1	HME
20-08-0600		-- No Outside Air Inlet/Outlet Connection Required	1	HME
20-10-1225		-- Work Light, (1) LED, 36" Strip Light, Mtd Pump Compt w/Switch	1	HME
20-12-0200		-- No Pump Enclosure Heater Required	1	HME
20-12-1000		-- No Heat Pan Enclosure Required	1	HME
20-14-0100		-- Pump Service Access Requirements	1	HME
20-14-0411		-- Control Panel, Top Mount Module - Gen IV	1	HME
20-15-0110		-- Identification Labels - Metal Tags	1	HME
20-15-0200		-- HME Standard Color Coding for Pump House Tags	1	HME
20-16-0200		-- Pump Panel Finish, Brushed Stainless Steel	1	HME

PART NO	S	DESCRIPTION	QTY	ID
20-18-0412		-- Controls & Gauges, Top Mount - FRC	1	HME
20-18-1420		-- FRC In Control 400 Pressure Governor, Engine Monitor and Pressure	1	HME
		Display		
20-18-1550		-- 2-1/2" Pressure Gauges, 0-400 psig - English	1	HME
20-18-1558		-- 2-1/2" Pressure Gauge LED Lighting	1	HME
20-18-1570		-- Pump Panel LED Lighting - WHITE/RED	1	HME
20-18-1998		-- No Control Panel Weather Cover Required	1	HME
20-18-2042		-- Drain Discharges - 90° Ports with Drain Tubing	1	HME
20-18-2404		-- Switch, Air Horn Activation, Mtd PPanel, Push Button w/Lbl	1	HME
20-18-2502		-- No Class 1 Flowminder Required At This Time	1	HME
20-18-2660		-- No Pump Panel Air Pressure Gauge Required	1	HME
20-18-2670		-- No Pump Panel Trans Temp Gauge Required	1	HME
20-18-2680		-- No Pump Panel Fuel Tank Gauge Required	1	HME
20-18-8000		-- No Pump Air Blow Out Required	1	HME
20-19-0002		-- No Pump Panel Radio Compt Required	1	HME
20-19-0098		-- No PPanel Radio Speaker Required	1	HME
30-26-0410		-- Gauge, (1) Water Tank Level - FRC Tank Vision	1	HME
30-26-0600		-- No Add'l Water Tank Level Gauge Required	1	HME
20-21-2424		-- Pump, Midship, Top, Darley "PSM", 1500 GPM	1	HME
20-26-2120		-- Pump Rating, Darley, 1500 GPM	1	HME
20-27-0100		-- Altitude Requirements, 0' to 2000 Feet Above Sea Level	1	HME
22-06-0904	>	-- Primer, Air Primer, Trident, On Darley Pump	1	HME
22-08-0200		-- Pump Shift, Pneumatic w/Label, Indicator Lgts, Mtd Cab/PPnl	1	HME
22-08-0500		-- No Pump Shift Override Required At This Time	1	HME
22-10-0825		-- Mechanical Seal, Inboard Side, Spring Loaded, Self Adjusting	1	HME
22-11-0200		-- Anode, Water Pump, Indicator Weep Hole	1	HME
22-14-1000		-- Thermal Relief Valve, TRV-L, Automatic	1	HME
22-14-1700		-- Intake Pressure Relief Valve, TFT	1	HME
22-18-0400		-- Master Drain, Class 1, Manual Mtd Pump Panel	1	HME
22-20-0100		-- Certified NFPA Pump Test, Completed Apparatus Certificate	1	HME
22-24-0200	S <	-- Pump Warranty, Darley, Five Year	1	HME
		No selectable Darley warranty available		
22-30-0200		-- Electronic Manuals, Pump Service and Operation	1	HME
		<b>Steamer Inlets</b>	<b>1</b>	<b>HME</b>
24-02-0410		-- Steamer Inlet, 6" NST Thread, L/S w/Strainer - No Intake Valves	1	HME
30-40-1060		-- Cap, 6" Long Handle - HME Logo	1	HME
30-40-2002		-- No Storz Adapter Required	1	HME
24-02-0510		-- Steamer Inlet, 6" NST Thread, R/S w/Strainer - No Intake Valves	1	HME
30-40-1060		-- Cap, 6" Long Handle - HME Logo	1	HME
30-40-2002		-- No Storz Adapter Required	1	HME
		<b>Intake Manifold(s)</b>	<b>1</b>	<b>HME</b>
24-02-2010		-- Stainless Intake Piping	1	HME
		<b>Left Side Small Intake</b>	<b>1</b>	<b>HME</b>
24-21-0028		-- Pump Side Intake, Left Side - Rear - Side Operated	1	HME
24-21-0425		-- Suction Inlet, Side 2.5" - Side Operated Module	1	HME
24-21-1025		-- Suction Valve Control, Push-Pull Type, Side, Adj To Valve	1	HME
30-40-1125		-- Intake Plug, (Qty) 2.5" w/Cap & Chain	1	HME
24-21-2000		-- No Left Forward Intake Required - Pump Side	1	HME
		<b>Left Side Pump Panel Discharges</b>	<b>1</b>	<b>HME</b>
26-03-0020		-- #1 Discharge, Left Side - Side Operated	1	HME
26-03-0425		-- Discharge, Side, 2.5" - 30 degree Elbow - Manual Control	1	HME
30-41-5025		-- Discharge Cap, (Qty) 2.5" Chrome Vented Rocker Lug w/Chain	1	HME
26-03-0030		-- #2 Discharge, Left Side - Side Operated	1	HME
26-03-0425		-- Discharge, Side, 2.5" - 30 degree Elbow - Manual Control	1	HME
30-41-5025		-- Discharge Cap, (Qty) 2.5" Chrome Vented Rocker Lug w/Chain	1	HME
		<b>Right Side Pump Panel Discharges</b>	<b>1</b>	<b>HME</b>
26-03-0220		-- #3 Discharge, Right Side - Side or Top Operated	1	HME
26-03-0425		-- Discharge, Side, 2.5" - 30 degree Elbow - Manual Control	1	HME
30-41-5025		-- Discharge Cap, (Qty) 2.5" Chrome Vented Rocker Lug w/Chain	1	HME
26-03-0230		-- #4 Discharge, Right Side - Side or Top Operated	1	HME
26-03-0430		-- Discharge, Side, 3" - 30 degree Elbow - Manual Control	1	HME
30-41-5030		-- Discharge Cap, (Qty) 3" Chrome Vented Rocker Lug w/Chain	1	HME
		<b>Discharge Manifold(s)</b>	<b>1</b>	<b>HME</b>
26-03-4010		-- Stainless Discharge Manifold	1	HME

PART NO	S	DESCRIPTION	QTY	ID
<b>Rear Discharges</b>				
26-06-0400		-- Discharge, 2.5" R/S Rear w/1/4Trn, SwngOut Vlv & 30Deg Elbw	1	HME
26-06-0500		-- No L/S Rear Discharge Required	1	HME
30-24-0400	>	-- Water Tank Sleeve, (1) 4" Rear Intake/Discharge	1	HME
30-41-5025		-- Discharge Cap, (Qty) 2.5" Chrome Vented Rocker Lug w/Chain	1	HME
30-41-6002		-- No Discharge Reducer Required	1	HME
<b>Front Bumper Jumphines</b>				
26-08-0200		-- No Front Jumphine Required	1	HME
<b>Deluge (Deck Gun) Piping</b>				
28-02-0400	>	-- Piping, 3" Deluge Riser, AbvPmp w/ 3" 1/4Trn & S/S Pipe	1	HME
26-12-0400		-- Drain Valve - Manual - Manual 1/4 Turn	1	HME
28-02-0555		-- Fixed Riser Piping, NPT Termination	1	HME
28-02-0800		-- Deck Gun Cntrl, 3" Manual Slow Close	1	HME
28-04-0200		-- No Monitor (Deck Gun) Required	1	HME
<b>Crosslay Assemblies</b>				
28-11-1100		-- Crosslay, (2) Beds, 1.5" NST / 1.5" NST - 47" Side	1	HME
28-11-5100		-- #1 Crosslay, Sngl Stk, 1-1/2" NST w/2" Piping and Valve	1	HME
26-12-0400		-- Drain Valve - Manual - Manual 1/4 Turn	1	HME
28-11-6100		-- #2 Crosslay, Sngl Stk, 1-1/2" NST w/2" Piping and Valve	1	HME
26-12-0400		-- Drain Valve - Manual - Manual 1/4 Turn	1	HME
28-11-7810		-- Crosslay Hose Guides	1	HME
28-12-2200		-- Cover, Crosslay, Vinyl w/End Flaps	1	HME
28-14-0400		-- Cover Color, Crosslay, Vinyl, Midnight Black	1	HME
<b>Left Dunnage Equipment - Generator, Hose Reel, Cord Reels</b>				
28-15-8102		-- No Left Dunnage Equipment Required	1	HME
<b>Right Dunnage Equipment - Generator, Hose Reel, Cord Reels</b>				
28-15-8200		-- SELECT Right Dunnage Equip HERE - *** Reels ***	1	HME
28-15-8202		-- No Right Dunnage Equipment Required	1	HME
<b>Ball Valves</b>				
30-00-0300		-- Ball Valves, Elkhart, Brass	1	HME
<b>Tank Plumbing and Indicators / Gauges</b>				
30-20-0600		-- Piping, Tank To Pump, 3" w/3" Air Operated Ball Valve	1	HME
30-20-2500		-- No Additional Tank To Pump Valve Control Required	1	HME
30-22-0400		-- Tank Refill, 2" Line w/ 1/4 Trn Bil Vlv	1	HME
<b>Top Mount Pumps</b>				
70-16-0010		-- No Spanner/Hydrant Wrenches Required	1	HME
<b>Foam Systems</b>				
20-32-0200		No Foam System Required	1	HME
<b>Compressed Air Foam Systems</b>				
20-32-5999		No CAFs System Required	1	HME
22-02-0800	>	Heat Exchanger Line, Gated, Custom	1	HME
<b>Discharge Special Thread Adapters</b>				
30-41-9002	>	No Special Discharge Thread Size/Pitch Required	1	HME
30-41-9003	>	No Special Intake Thread Size/Pitch Required	1	HME
<b>== Pumper Components &amp; Equipment - 4.001 ==</b>				
08-22-2001	>	Apparatus Body Designation, Model Ahrens-Fox	1	HME
<b>Water / Foam Tanks and Equipment</b>				
30-02-0300		Water Tank Cnstrctn, Poly w/Tnk Lid, FillTwr, Ovrfw	1	HME
30-14-0200		-- No Foam Tank Required	1	HME
30-18-0200		-- Tank Mounting, Cradle Mtd, 8" x 8" x 4" x .250"	1	HME
30-18-0600		-- Tank Cradle - Painted to Match Axles Color	1	HME
30-21-0100		-- No Tank Drain Valve Required	1	HME
<b>APPARATUS BODY DESIGN AND CONSTRUCTION</b>				
32-02-0200		Body Design and Construction, Pumper, Stainless Steel	1	HME
32-02-9000		-- Compartment Interior Finish	1	HME
32-05-0100		-- Brushed Stainless Compartment Roof - Not a Stepping Surface	1	HME
46-18-1000		-- Rear Tailboard, 12", LaserGrip Stainless Steel	1	HME
46-22-0200		-- No Rear Lower Step/Platform Required	1	HME
<b>EXTERIOR COMPARTMENTATION AND EQUIPMENT</b>				
40-01-2110		Frame Extension, Rear	1	HME
40-01-2200		-- Rear Frame Extension - Painted to Match Frame Color	1	HME
40-02-0200		Ext Compartment Design and Construction, Modular, Bolted	1	HME
40-02-0204		-- Compartment Ventilation w/Filtration	1	HME
46-28-0710		-- No Exhaust Tailpipe Heatshield Required	1	HME
40-06-0200		Medium Body Configs, Approx 500 - 1370 Gallon Capacities	1	HME

PART NO	S	DESCRIPTION	QTY	ID
40-06-1000	>	-- 7) 74"/74", FH/RD Ext Cmpts w/ThruTnk, TTnk, 1206-1440-1596Gls, 63", 69", 73" HB	1	HME
30-08-2200	S	-- Water Tank Capacity, T-Tank, 1045 US Gallons - TT - 7 63" HB	1	HME
30-02-1000		-- Tank Fill Tower, 10" x 14", w/4" Vent	1	HME
30-12-3200		-- Cubic Ft, Body 159, 148" OAL	1	HME
30-23-0012	>	-- No Left Rear Direct Tank Fill Required	1	HME
30-23-1022	>	-- No Right Rear Direct Tank Fill Required	1	HME
		<b>HOSEBED</b>	<b>1</b>	<b>HME</b>
34-02-0020		-- Hosebed, Double High Side Pumper Body - Ladders Thru & Beam	1	HME
34-03-0210		-- Hosebed, 14" Walls, Double High Side	1	HME
		<b>Hard Suction Tray - 10 Foot</b>	<b>1</b>	<b>HME</b>
46-29-0010		-- No L/S Hard Suction Trays Required	1	HME
46-29-1010		-- No R/S Hard Suction Trays Required	1	HME
34-04-0600	>	-- Dividers, (Qty) Hosebed, Adjustable, Smth Alum w/Radius Crnr	2	HME
34-06-0400		-- Hosebed Cover, Black	1	HME
34-06-2001		-- No Lettering On Hosebed Cover Rear Flap Required	1	HME
		<b>LEFT SIDE EXTERIOR COMPARTMENT DIMENSIONS</b>	<b>1</b>	<b>HME</b>
40-12-1400		-- 74"/74", Ext Cmpts, L/S, 48"/52"/43" W x 12"/24" D, FH/RD	1	HME
40-14-1001		-- No Air Outlet Connection Required	1	HME
40-15-0140		-- Roll Up Doors, L/S, Satin Anodized Finish - Med Bdy - LSL	1	HME
40-16-0400		-- Door Latches, L/S, Non-Locking Lift Bar w/Door Ajar Switch	1	HME
40-18-0200		-- No L/S Rollup Door Straps Required At This Time	1	HME
46-08-1199		-- No Roll-Up Door Shields Required	1	HME
		<b>FENDER CONFIGURATIONS</b>	<b>1</b>	<b>HME</b>
41-00-0400		-- Wheel Area, Single Axle, - Rr SCBA Tubes - FFS	1	HME
46-02-0600		-- No Fuel Fill w/Cover Required At This Time	1	HME
46-06-0400		-- Fenderettes and Wheel Well Liners - Stainless	1	HME
46-08-0200		-- Mud Flaps, Rear	1	HME
46-28-0400		-- SCBA Tubes, (4) Rear Wheelwell, (2) L/S - (2) R/S, Sngl Axle	1	HME
46-28-0680		-- SCBA Bottle Retention Strap(s)	1	HME
		<b>RIGHT SIDE EXTERIOR COMPARTMENT DIMENSIONS</b>	<b>1</b>	<b>HME</b>
42-02-1600		-- 74"/74", Ext Cmpts, R/S, 48"/52"/43" W x 12"/24" D, FH/RD	1	HME
42-07-0140		-- Roll Up Doors, R/S, Satin Anodized Finish - Med Bdy - LSL	1	HME
42-08-0400		-- Door Latches, R/S, Non-Locking Lift Bar w/Door Ajar Switch	1	HME
42-10-0200		-- No R/S Rollup Door Straps Required	1	HME
46-08-1199		-- No Roll-Up Door Shields Required	1	HME
		<b>EXTERIOR BODY COMPONENTS</b>	<b>1</b>	<b>HME</b>
46-05-0630		-- Rubrail, Body, LED Strip, Armor Guard, Warning/Ground - Medium Body	1	HME
46-05-1000		-- No Rub Rail Conspicuity Tape Required	1	HME
46-06-0462		-- Painted Apparatus Body - Pumper	1	HME
46-06-0602		-- Painted Apparatus Body, Wheel Well Fender Panels	1	HME
46-06-0603		-- No Painted Body Front Corner Panels Required	1	HME
46-06-0605		-- No Painted Body Rear Corner Panels Required	1	HME
46-06-0610	>	-- Painted Hosebed / Coffin Cmpt Exterior Side Walls	1	HME
46-06-0612	>	-- Painted Hosebed / Coffin Cmpt Exterior Front Wall	1	HME
46-06-0614		-- No Painted Area Between Doors Required	1	HME
46-06-0800		-- No Paint Spray Out Approval Sample Required	1	HME
46-10-0700		-- Lights, Compartment, LED Strip, Armor Protected - White/Red	1	HME
46-15-0100		-- Pumper Body Rear Config - Ladders Thru the Tank - 63", 69", 73" HB	1	HME
		<b>REAR BODY CENTER</b>	<b>1</b>	<b>HME</b>
46-15-0410		-- Rear - Center - RR1 Half Height - 63" 69" 73" HB	1	HME
42-12-0200		-- RR1, Ext Cmpt, Rear, 29" H x 48" W x 22" D, Half Height	1	HME
30-32-0200		-- No Rear Dump Valve Required	1	HME
42-23-0100		-- Roll Up Door, Rear, Satin Anodized Finish, Half Height	1	HME
42-26-0200		-- Door Latch, Rear, Non-Locking Lift Bar w/Door Ajar Switch	1	HME
42-32-0200		-- No Rear Rollup Door Straps Required	1	HME
46-08-1199		-- No Roll-Up Door Shields Required	1	HME
84-04-5010		-- Chevron, Rear Body NFPA, 6" - Pumper Low Rear Door	1	HME
84-04-8002		-- Chevron Color - Red and Yellow Reflective	1	HME
42-14-0210	>	-- RR2, Ladder Stg Cmpt, Rear - Thru Tank - Std w/Multi Opt	1	HME
42-16-0400		-- Cover, Alum, Bolt-On, Mtd Inside Pmp Cmpt, Prtct Ladders	1	HME
42-18-0410	>	-- RR2a, Multipurpose Storage, Inside Tank Cmpt, Upper Rear	1	HME
42-18-0520	>	-- Second Cmpt - (3) 6" Suction and Long Handled Tools	1	HME
42-28-0200		-- Hinged Door, Rear, Ladder Storage	1	HME
42-32-0710		-- Lighting, Rear Ladder Compartment	1	HME

PART NO	S	DESCRIPTION	QTY	ID
46-26-0810		-- Lighting, White Color	1	HME
72-00-0010		-- Thru The Tank Ladder Group - 10-Fold, 14-Roof, 24-2 Sec	1	HME
72-04-0400		-- Ladder, 14' Roof, Duo-Safety, Channel Rail, Aluminum	1	HME
72-06-0400		-- Ladder, 10' Fldng Attic, Duo-Safety, Aluminum	1	HME
72-08-0400		-- Ladder, 24' Two-Sect Ext, Duo-Safety, Solid Beam Aluminum	1	HME
72-18-0100		-- No Pike Pole(s) w/Fiberglass Handles Required	1	HME
72-18-0110		-- No Pike Pole(s) w/Fiberglass Handles Required	1	HME
72-18-0200		-- No Pike Pole(s) w/Fiberglass Handles Required	1	HME
72-18-0210		-- No Pike Pole(s) w/Fiberglass Handles Required	1	HME
72-18-0300		-- No Pike Pole(s) w/Fiberglass Handles Required	1	HME
46-20-0100		-- Step, Intermediate, mid position, Laser Grip, 8" Deep x Full Width	1	HME
46-12-0250		-- Lights, Rear Body, LED Strip Intermediate Step, Activate w/Parking	1	HME
	Brk			
46-26-0100		-- Handrail, Rear, 69" Horizontal Hosebed	1	HME
46-26-0710		-- Lighting, Rear Horizontal Handrails	1	HME
46-26-0810		-- Lighting, White Color	1	HME
		<b>REAR BODY LEFT SIDE</b>	<b>1</b>	<b>HME</b>
46-15-0510		-- Rear - Left Side - Egress Steps - one (1) folding step, lower (1) fixed	1	HME
	step			
46-16-0012		-- Step, Folding, (1) Mounted Left Rear Upper Position	1	HME
46-18-0700		-- Standard Folding Step	1	HME
46-20-0110		-- Steps, Intermediate, (1) Lower, Left Corner, Laser Grip, 8" Deep	1	HME
46-26-0110		-- Handrail, Rear Left Side, 24" Vertical	1	HME
		<b>REAR BODY RIGHT SIDE</b>	<b>1</b>	<b>HME</b>
46-15-0610		-- Rear - Right Side - Egress Steps - upper (1) folding step, lower (1) fixed	1	HME
	step			
46-16-0014		-- Step, Folding, (1) Mounted Right Rear Upper Position	1	HME
46-18-0700		-- Standard Folding Step	1	HME
46-20-0112		-- Steps, Intermediate, (1) Lower, Right Corner, Laser Grip, 8" Deep	1	HME
46-26-0120		-- Handrail, Rear Right Side, 24" Vertical	1	HME
46-16-0305		-- Steps, (4) Four, Folding, Mounted Front of Body, Per NFPA	1	HME
46-18-0700		-- Standard Folding Step	4	HME
46-16-0307		-- Steps, Folding, 2-Extra Mounted Front of Body	1	HME
46-18-0700		-- Standard Folding Step	2	HME
		<b>Exterior Body Equipment / Mounting Devices</b>	<b>1</b>	<b>HME</b>
58-02-0100		-- Floodlight, Maxxima, (1) MWL-36, 2100 Lumens, Mnt Frt R/S Hsbd	1	HME
58-02-0104		-- No Front Hosebed Light Remote Switch Required At This Time	1	HME
		<b>SCENE LIGHTING - PUMPER / RESCUE</b>	<b>1</b>	<b>HME</b>
58-09-1010		-- No Cab Side Scene Lights Required	1	HME
58-09-2010		-- No PPanel Side Scene Lights Required	1	HME
58-09-3010		-- No Body Side Scene Lights Required	1	HME
58-09-4010		-- No Body Rear Scene Lights Required	1	HME
58-09-4610		-- No Apparatus Perimeter Enhancement Lights Required	1	HME
		<b>CAB FRONT AND SIDE / QUARTZ AND LED LIGHTING</b>	<b>1</b>	<b>HME</b>
58-10-8004		-- No Forward Cab Quartz/LED Lighting Required	1	HME
58-10-8006		-- No Side Quartz/LED Lighting - Custom Cab Roof - Required	1	HME
		<b>CAB REAR QUARTZ LIGHTING</b>	<b>1</b>	<b>HME</b>
58-12-9060		-- No Quartz Lighting - Custom Cab Left Rear Wall - Required	1	HME
58-12-9070		-- No Quartz Lighting - Custom Cab Right Rear Wall - Required	1	HME
		<b>BODY QUARTZ LIGHTING</b>	<b>1</b>	<b>HME</b>
58-14-0100		-- FRC - LF Corner - High Side	1	HME
58-15-1008		-- FRC, Evolution II, LED DC 11K LM	1	HME
58-15-8002		-- No Lamphead Switch Required	1	HME
58-15-8006		-- No Lamp Wire Guard Required	1	HME
58-18-0100		-- No Remote Switch for Quartz Light Required - Cab	1	HME
58-18-0204		-- Switch, Remote, 12 V w/240V Relay, Mtd Pump Panel	1	HME
58-15-8010		-- FRC, Bottom Raise Pole - 530	1	HME
58-14-0110		-- FRC - RF Corner - High Side	1	HME
58-15-1008		-- FRC, Evolution II, LED DC 11K LM	1	HME
58-15-8002		-- No Lamphead Switch Required	1	HME
58-15-8006		-- No Lamp Wire Guard Required	1	HME
58-18-0100		-- No Remote Switch for Quartz Light Required - Cab	1	HME
58-18-0204		-- Switch, Remote, 12 V w/240V Relay, Mtd Pump Panel	1	HME
58-15-8010		-- FRC, Bottom Raise Pole - 530	1	HME
58-13-0130		-- No Quartz Lighting - Lft Rr Body Corner Required	1	HME

PART NO	S	DESCRIPTION	QTY	ID
<b>RECEIVER HITCH / PORTABLE WINCH</b>				
46-36-0210		-- No Rear - Receiver Hitch Required	1	HME
46-36-0220		-- No Driver's Side - Receiver Hitch Required	1	HME
46-36-0230		-- No Officer's Side - Receiver Hitch Required	1	HME
46-36-0240		-- No Front - Receiver Hitch Required	1	HME
46-40-0100		-- No Portable Winch Required	1	HME
<b>SHELVES</b>				
48-02-0200		No DEEP 24" Adjustable Shel(ves) Required	1	HME
48-03-0600		Shelves Shallow, (Qty) Adjustable w/1.5" Flange, .190" Alu	4	HME
48-03-1000	S	>  -- Shelves Location, Specify Ext Compts	4	HME
48-08-0200		-- No Matting on Shel(ves)/Tray(s) Required	4	HME
<b>TRAYS</b>				
48-04-1600		> Trays, (Qty), Pullout w/Slides & Gas Shck, .190" Alm 250#	4	HME
48-04-2000	S	-- Pullout Trays, Locations, Specify Ext Compts	4	HME
48-08-0200		-- No Matting on Shel(ves)/Tray(s) Required	4	HME
48-04-2190		No Heavy Duty Pullout Tray(s) Required - 500#	1	HME
<b>AJUSTABLE TRAYS</b>				
48-04-2399		No Adjustable Pullout Tray(s) Required	1	HME
<b>OUT AND DOWN SHELVES</b>				
48-06-0600		Trays, (Qty) Pull Out & Down w/Slides, .190" Alum, 250#	1	HME
48-06-1000	S	-- Pullout & Down Trays, Locations, Specify Ext Compts	1	HME
48-08-0200		-- No Matting on Shel(ves)/Tray(s) Required	1	HME
48-10-0200		No Dri-Dek on Compartment Floors Required	1	HME
<b>FOXTRAX</b>				
48-14-0200		No FoxTrax Alum Toolboard In Compts Required	1	HME
<b>VERTICAL DIVIDERS AND TOOLBOARDS</b>				
48-16-0200		No Ext Compt Vertical Divider(s) Required	1	HME
48-18-0100		No Slide Out Vertical Tool Boards Required	1	HME
48-18-0400		Vertical Toolboard, Swing-Out	1	HME
48-18-1000		>  -- FoxTrax, {qty} Alum Tool Mounting Extrusions, Mtd Tool Brds	1	HME
48-18-1200	S	-- Vertical Toolboard Location, Specify Ext Compt	1	HME
<b>POLY BINS</b>				
48-22-0200		No Poly Bins Required	1	HME
<b>TOOL BOXES</b>				
48-24-0100		No Tool Boxes Required	1	HME
<b>12 VOLT ELECTRICAL SYSTEM</b>				
50-02-0200		Electrical System, 12V, Body, Multiplexed w/Circuit Brkr Pnl	1	HME
<b>DIESEL AND GAS GENERATORS AND COMPONENTS</b>				
52-02-0200		No Diesel Generator Required	1	HME
52-04-0200		No Gas Generator Required	1	HME
<b>LIGHTING SELECTION</b>				
54-90-0100		MAKE ICC AND WARNING LIGHT SELECTIONS HERE	1	HME
55-01-0020		-- Commercial Cab - Double Hi Side Body	1	HME
55-02-2000		-- Body - LED - ICC Lighting with Body Side Clearance LED & Reflector	1	HME
55-03-0200		-- No 'Rookie Rods' with Light Required	1	HME
55-05-0100		-- No Cab Side Turn Signal Required	1	HME
55-05-0132		-- Rear Stop/Tail/Turn - Whelen	1	HME
55-05-0142		-- Halogen Backup Lights - Whelen	1	HME
55-05-0200		-- No Body Side Turn Signal Required	1	HME
55-06-0480		-- Back Up Alarm	1	HME
55-06-0500		-- No Center Rear Brake Light Required	1	HME
55-06-0600		-- No Backup Light Remote Switching Required	1	HME
55-06-1000		-- License Plate Bracket w/LED Light	1	HME
57-01-0334		-- Whelen - LED - COMMERCIAL Pumper/Tanker/Rescue	1	HME
55-05-0300		-- No Body Corner Marker / Warning Light Required	1	HME
57-04-3302		-- Lightbar, Frt, Whelen - Freedom - LED	1	HME
57-10-1005		-- No Opticon Option Required - Lightbar Mounted	1	HME
57-10-0000		-- No Opticon Option Required - Separate Roof Mounted	1	HME
57-20-3304		-- Grille, Frt, Whelen - C6 SurfaceMax Series - Super LED	1	HME
57-03-1000		-- Lens Color - Both Red	1	HME
57-30-0000		-- No Front Bumper Intersection Lights Required	1	HME
57-31-3304		-- Hood Side, Whelen - C6 SurfaceMax Series - Super LED	1	HME
57-03-1000		-- Lens Color - Both Red	1	HME
57-80-0000		-- No High Beam Alternating Headlight Warning Lights Required	1	HME
57-02-0326		-- Whelen - LED - Double Hi Side Body	1	HME

PART NO	S	DESCRIPTION	QTY	ID
57-34-3304		-- Body, Side Over Wheel, Whelen - C6 SurfaceMax Series - Super LED	1	HME
57-03-1000		-- Lens Color - Both Red	1	HME
57-40-3308		-- Upper Rear, Whelen - Micro Edge Lightheads w/Stanchions	1	HME
57-03-1000		-- Lens Color - Both Red	1	HME
57-42-3304		-- Lower Rear, Whelen - C6 SurfaceMax Series - Super LED	1	HME
57-03-1000		-- Lens Color - Both Red	1	HME
57-44-0000		-- No Rear Body Traffic Advisor Light Required	1	HME
58-21-0010		No Light Tower Required	1	HME
58-22-0200		No Apparatus Light Tower Required	1	HME
58-24-0200		No Rear Hosebed Mtd Spot/Flood Lights Required	1	HME
		<b>COMMUNICATION, MISC EQUIPMENT, LADDERS</b>	<b>1</b>	<b>HME</b>
70-02-0400		Labels, Identification & Safety, Mtd Drvr's Compt/Pump Panel	1	HME
70-04-0200		No Fire Extinguisher(s) Required	1	HME
70-06-0200		No Portable Handlight(s) Required	1	HME
70-12-0200		No Flathead Axe(s) Required	1	HME
70-12-1200		No Pickhead Axe(s) Required	1	HME
70-20-0200		No Salvage Cover(s) Required	1	HME
70-22-0200		No Backboard(s) Required	1	HME
70-24-1000		Wheel Chocks, (2) Worden HWGY, Yellow Alum w/Sld-Out Brkt	1	HME
70-26-0200		No SCBA Bracket(s) Required	1	HME
70-28-0200		No SCBA Storage Rack Required	1	HME
		<b>Pike Poles</b>	<b>1</b>	<b>HME</b>
72-18-0100		No Pike Pole(s) w/Fiberglass Handles Required	1	HME
72-18-0200		No Pike Pole(s) w/Fiberglass Handles Required	1	HME
72-18-0300		No Pike Pole(s) w/Fiberglass Handles Required	1	HME
72-22-0100		No Pike Pole(s) w/Wood Handles Required	1	HME
72-22-0200		No Pike Pole(s) w/Wood Handles Required	1	HME
72-22-0300		No Pike Pole(s) w/Wood Handles Required	1	HME
		<b>ELECTRIC CORD REELS AND COMPONENTS</b>	<b>1</b>	<b>HME</b>
74-02-0200		No Electric Cable Reel Required	1	HME
		<b>HYDRAULIC HOSE REELS</b>	<b>1</b>	<b>HME</b>
74-12-0200		No Hydraulic Hose Reel Required	1	HME
		<b>UTILITY AIR REELS</b>	<b>1</b>	<b>HME</b>
74-22-0200		No Utility Air Hose Reel Required	1	HME
74-34-0100		No Hydraulic Rescue Tool Power Units Required	1	HME
74-35-0100		No Hydraulic Rescue Cutters/Spreaders Required	1	HME
74-38-0100		No Hydraulic Rescue Tool Accessories Required	1	HME
74-40-0100		No Hydraulic Rescue Tool Rams Required	1	HME
		<b>HARD SUCTION HOSE</b>	<b>1</b>	<b>HME</b>
76-02-0200		No Hard Suction Hose Required	1	HME
76-02-0201		No Additional Hard Suction Hose Required	1	HME
		<b>SUCTION STRAINERS</b>	<b>1</b>	<b>HME</b>
76-06-0200		No Suction Strainer Required At This Time	1	HME
76-06-0201		No Additional Suction Strainer Required	1	HME
78-24-0190		No Refrigerator Required	1	HME
		<b>REFLECTIVE STRIPING</b>	<b>1</b>	<b>HME</b>
84-02-0800		Striping, 4" Scotchlite, Reflective, Vehicle Perimetr	1	HME
84-04-1202		-- No Stripe Flare Required	1	HME
84-04-3010		-- Base Stripe Color, White Reflective	1	HME
84-04-4002		-- No Stripe Outline Required	1	HME
84-04-2898		No Shelf Edge Striping Required	1	HME
84-05-0011		No Lettering Required	1	HME
84-06-4000		No "Keep Back" Warning Sign Required	1	HME
		<b>MISC. ITEMS</b>	<b>1</b>	<b>HME</b>
86-02-0001		No Miscellaneous Fastener Kit Required	1	HME
		<b>WARRANTIES, MANUALS, MISCELLANEOUS DOCUMENTS</b>	<b>1</b>	<b>HME</b>
90-03-1000		Water Tank Warranty - Service Life	1	HME
		<b>v4.001 - RELEASE DATE - 03/01/2018</b>	<b>1</b>	<b>HME</b>
		<b>== Limited Warranty - Use For Contracts - 4.001 ==</b>	<b>1</b>	<b>HM</b>
10-00-0030		Limited Warranty	1	HM
20-02-0030		-- General Warranty Period - 3 Years Total	1	HM
40-00-0005		-- Cab & Body Paint Warranty Period - 5 Years	1	HM
		<b>v6.001 - RELEASE DATE - 12/31/2019</b>	<b>1</b>	<b>HM</b>